

# PET, IODINE, or Tc-99m DTPA AIR MONITOR GAS & PARTICULATE

## Model - FM-9-ABNI

### FEATURES:

- DETECTS POSITRON, IODINE, Tc-99m DTPA
- AIRBORNE CONCENTRATION
- INTEGRATED EXPOSURE
- HIGH SENSITIVITY
- REAL TIME ALARM
- LINE OPERATED
- STANDARD FM-9 MODULES
- CAN DRAW AIR FROM HOOD, DUCT, ETC.
- QUICK CHANGE FILTER CARTRIDGE
- REGULATED AIR FLOW
- BUILT-IN DATA ARCHIVE & RETRIEVAL
- DATA UPDATES EVERY FEW SECONDS – OPERATOR SETTABLE
- COMPUTER INTERFACE – USB OR ETHERNET
- TRANSPORTABLE / CART MOUNTED UNIT AVAILABLE
- OPTION: Bq/m<sup>3</sup> or Ci/l

FM-9-ABNI



Detector PGS-31

### USERS:

- Hospitals / Research
- Power Plants
- National Labs

### APPLICATION:

The **FM-9- ABNI** Air Monitors assure safety against airborne radioactivity contamination by means of constant check with alarm and record capability.

It provides integrated exposure information and can provide hard copy via external printer or computer. It is a complete system and may be expanded per need with modules of the **FM-9** series.

The **FM-9- ABNI** may be used to monitor stack effluent down to EPA levels as well as hoods, glove box or workplace air.

#### **HOSPITALS: Protect workers, patients & the public.**

- Use as Iodine Monitor for thyroid assessment & treatment areas
- Use as a Positron Monitor for all PET scan facilities.
- Use as a Tc-99m DTPA Air Monitor for areas where bone scans and DTPA lung function studies take place.

#### **POWER PLANTS: Protect Workers & the community**

- Use in radiation building.
- Use in containment.
- Use in the chemistry lab.
- For detection of Iodine & other radio chemicals.

#### **NATIONAL LABORATORIES: Protect workers & the public**

- Sees airborne particulates.
- Sees airborne radio chemicals of all types except Noble Gases

# PET, IODINE, or Tc-99m DTPA AIR MONITOR GAS & PARTICULATE

## Model - FM-9-ABNI

### DESCRIPTION:

The **FM-9- ABNI** uses a standard charcoal filter in TA's unique quick change, no leak holder to trap any airborne Radio Iodine. The filter is under constant surveillance via a thin window scintillation detector. Air is drawn by a regulated pump through a three-foot inlet hose and exhausted via a flow meter through another three-foot hose.

These may be extended to allow monitoring of hoods, glove boxes, stacks, etc. Time is recorded by an odometer type timer wired into the pump circuit.

The unit is completely self-contained and portable. Complete with 10 filter cartridges.

PUMP: 56 liter/minute		PUMP: 120 liter/minute	
Time	Sensitivity	Time	Sensitivity
10 sec	$5 \times 10^{-3} \mu\text{Ci/l}$	10 sec	$2 \times 10^{-3} \mu\text{Ci/l}$
2 min	$1 \times 10^{-4} \mu\text{Ci/l}$	2 min	$0.5 \times 10^{-5} \mu\text{Ci/l}$
60 min	$8 \times 10^{-7} \mu\text{Ci/l}$	60 min	$3 \times 10^{-7} \mu\text{Ci/l}$
8 hr	$8 \times 10^{-8} \mu\text{Ci/l}$	8 hr	$4 \times 10^{-8} \mu\text{Ci/l}$
1 Week	$8 \times 10^{-13} \mu\text{Ci/l}$	1 Week	$8 \times 10^{-11} \mu\text{Ci/l}$

This corresponds to  $2 \times 10^{-7} \mu\text{Ci/ml}$  minute exposure which is equal to 0.6% of the California Safety Code Title 17  $10^{-10}$  and USNRC Title 10 limit 40 hour weekly exposure to most hazardous Beta and/or Gamma emitter in absence for of Ac 227.

### DETECTOR:

**Model PGS-3** for sensitivity to **ALL** Iodines and Positron emitters.

2" diameter probe with thin window, 1"x 1" thick crystal, scintillation detector.

### ELECTRONIC MODULES INCLUDE:

**Power Supply and MV-5.12.24.**

**MAC-5:** Air Control Timer; Low Flow Alarm Flowmeter

**MGA-5:** Single Channel Analyzer

**MCT:** On-Board computer with color monitor

### WEIGHT AND DIMENSIONS:

ITEM	WEIGHT	DIMENSION
Electronics	20 lbs	21W x 16D x 11H
Pump	8 lbs	6W x 6D x 8H
Detector Shield with Detector	30 lbs	13L x 6W x 6H
Shipping Weight	65 lbs	



**TECHNICAL ASSOCIATES** Divisions of



US NUCLEAR CORP



W: [www.activeradsys.it](http://www.activeradsys.it) Tel: 0544 408071  
E: [info@activeradsys.it](mailto:info@activeradsys.it) Fax: 0544 201477